ROTATOR / SHAKER

BLOOD PIPETTE SHAKER

PS-600T & PS-800T



Fastures:

- Blood pipette shaker is an electric vibrator for blood diluting pipettes which provides an uniform mixing of the chemicals with blood to be tested due to its controlled agitation.
- PS-600T has a pipette holder made of stainless steel spring clips.
- * The holder of PS-800T is made of rubber.
- * PS-600T can provide continuous or timing operation (0-15min.).
- * PS-800T provide timing operation (0-15min.) and 3-section speed.
- * Quality certification: ISO 9001

PS-600T

PS-800T

Specifications:

	Model	Capacity	Switch	Speed	Size (mm) (W×D×H) 150×135×160	Weight (kg) (N.W. / G.W.) 1.8 / 2.2	
	PS-600T	6 pipettes	3 positions (ON/OFF/TIMER 0-15min.)	2,500rpm (fixed)			
	PS-800T	8 pipettes	0-15 min. mechanical timer	3-section vibration speed	140×180×110	1.6 / 2.0	
٠,							

Power Supply: AC110V 60Hz (220V 50/60Hz available)

MICRO SHAKER

MS-1000



Features.

- Micro shaker MS-1000 is used in PHA, R-PHA, EIA, RIA, ELESA for micro assay plates with 96 well. Also suitable for use HBS, HBC, TPHA, RUBELLA etc.
- * Table top design can save your bench space.
- * MS-1000 provides 3-sectoin vibration speed to meet your requirement.
- Quality certification: ISO 9001

MS-1000

Specifications:

Model	Speed	Timer (min.)	Platform size (mm) (W×D)	Size (mm) (W×D×H)	Weight (kg) (N.W. / G.W.)
MS-1000	3-section vibration speed	0-15 min. mechanical timer	90×132	110×180×100	1.5 / 1.8

Power Supply: AC110V 60Hz (220V 50/60Hz available)

SUSPENSION ROTATOR

SR-100



Features

- 3D gyratory movement provides consistently uniform specimen quality in one minutes.
- Large capacity of tray holds a variety of sizes and shapes of containers such as tubes and vials.
- Rubber dimple mat of tray firmly but gently holds containers.
- Test containers can be easily loaded and unloaded without turning the unit off.
- Quality certification: ISO 9001

Specifications:

Model	Speed	Movement	Switch	Tray size (mm) (W×D)	Size (mm) (W×D×H)	Weight (kg) (N.W. / G.W.)
SR-100	30rpm at 60Hz; 25rpm at 50Hz	3D gyratory movement on a central point	ON/OFF	230×125	230×125×175	1.8 / 2.1

Power Supply: AC110V 60Hz (220V 50/60Hz available)

Te1:886-2-7708-6789 Fax:886-2-7708-6799

http://www.aron.com.tw